## Macro

## Distortionless SERIES

Precision without distortion













## **Features**

The VS-LDA series generates a low distortion image, even when using extension tubes, by using a large number of lens shifts. Its design allows for the support of a wide range of magnification, WD, and DOF.

Model	Focal Length	Magnification	Working F/#
VS-LDA4	4	(∞) 0.01x - 0.04x	2.1
VS-LDA6.5	6.5	(∞) 0.01x - 0.6x	2.3
VS-LDA10	10	(∞) 0.03x - 0.1x	2.3 - 2.4
VS-LDA15	15	(∞) 0.03x - 0.15x	2.1 - 2.2
VS-LDA20	20	0.04x - 0.22x	2.1 - 2.3
VS-LDA25	25	0.05x - 0.25x	2.1 - 2.6
VS-LDA30	30	0.08x - 0.23x	2.4 - 2.8
VS-LDA35	35	0.30x - 0.50x	2.5 - 2.9
VS-LDA50	50	0.10x - 0.25x	2.7 - 3.1
VS-LDA75	75	0.15x - 0.35x	4.1 - 4.5

Compared to a conventional fixed focal length lens, the image generated by a VS-LDA lens is not distorted even towards the edges of the lens.

VS-LDA			
1 硫酸锶			
		職職	
Convetional Lens			
日 田 田 田 田		國際	
医医腹膜	超麗麗		
	100 NO. 300		

## **Application**

Having low distortion and good contrast is especially useful for measurement applications or applications that require a clear image from the entire available FOV. In the below example, the distortion and low contrast in convetional lenses makes it difficult to read QR codes that are far from the lens center while the VS-LDA series performs well throughout the entire FOV. If you have a QR Reader you can test it for yourself!

